

www.tsms.kr



TSM ECONOLOGY

Please experience the next generation reflow which takes measures effectively against the CO₂ regulation, which has been further upgraded through the addition of full line–up of N_2 gas system supplying high purity and low dew point N_2 gas stably by realizing the lowest power and N_2 consumption.







Please scan the QR code using a smart phone.

Reflow Line-up G stem



Twin Reflow

for Automobiles /

Medical Appliances, etc.



Dual Reflow

Appliances, etc.



TVs / Computers / Mobile Phones / LEDs / BLUs / Set–top Boxes /

Electrical and Electronic Equipment

for Automobiles / Medical





Compact / Slim Reflow Flip Chips / BGAs / Pre-flux, etc.

LED / BLU Reflow Large LEDs / BLUs / Lighting /

Large Test Boards / TVs



TVs / Computers / Mobile Phones / LEDs / BLUs / Set-top Boxes /

Electrical and Electronic Equipment

Vacuum Reflow (Technical cooperation with ETC) Power Devices, etc.

Semiconductor Reflow Flip chip / Bonding Package



ES-Reflow - Ultra power cost saving - Outstanding thermal efficiency



TRA Reflow

TVs / Computers / LEDs / BLUs / Set-top Boxes / Electrical and Electronic Equipment for Automobiles / Medical Appliances, etc.



Single-sided Reflow

Alternative Use for Wave Soldering Power Boards / Electrical and Electronic Equipment for Automobiles / Set-top Boxes, etc.



TRN-Reflow

- Maximization of Heat Efficiency through Triple Heat Insulation
- Improved maintainability
- Flux suppression system
- Electrical and Electronic Equipment Containing Large Amount of Flux – Improved Flux Recovery Function
- (2 times compared to the existing function)



Section 2 Se Supplies high purity N2 gas to the N2 Reflow stably

Features of Reflow

Less than

29KW



Convenient $\mathbf{\Sigma}$ Screen Configurationa Provides the convenience of user access and reading by splitting the MMI \leftrightarrow RTPM ↔ Rppm programs for the user interface into three screens on a wide monitor.



Rppm / Option

The real time O₂ concentration profile system, Rppm, provides the ppm information of each zone by measuring the purity of oxygen inside the oven in real time and maintains the N2 atmosphere constantly by measuring it repeatedly



Less than 9KW at idling state



The N₂ flow control method allows as much N2 to be consumed as is needed to maintain the ppm inside the reflow oven. (In the case of existing O2 flow control methods, energy loss occurs regardless of the set ppm by consuming N2 flow rate control according to the ppm setup quantitatively.)

Ω



Power Consumption at Idling State

The N70-e series model, developed ourselves, reduces power consumption significantly compared to other existing systems



O2 Control System

zones)

Realizes highly accurate O2 concentration

concentration. (Uniform control of entire

through automatic control of the O2

rimary startup power : 47KW Secondary startup power : 42KW

Less than 10KW at idling state



Dual Conveyor / Option (Σ) Dual Lane (Option) Increased productivity (Compared to existing single lane systems) Maximized extendibility and convenience → applicable to the maximum width of a dual lane system: 400mm

Fixed axis to be arranged according to

customers' needs → FMMF/ FMFM

(F: fixed, M: movable)



The real time temperature profile system,

further provides a variety of information as

well as a process index and chart data for

the analysis of compatibility and process

RTPM, which has evolved one step

RTPM / Option

capability

 (Σ)

Special Heater / Option The special panel heater developed by TSM exhibits outstanding thermal efficiency and profile reproducibility by utilizing the radiant heat and existing convection current generated from the nanel itself



Dilt-in PSA / Option

Built-in PSAs interlocked with a reflow allow innovative use of space and provide users with a stable operation environment by performing precise PC control of large capacity PSAs supplying high purity nitrogen



Surface Temperature $\mathbf{\Sigma}$ The reflow is insulated so that its surface temperature will have little influence on operators and the HVAC system, resulting in low power consumption



S TMS (TSM reflow Mobile / Server Monitoring Service) / option

> It is possible to check the reflow operation status, operation mode, alarms and abnormal states, etc., in real time from a smart phone and server PC (Max 100 lines)



FMS(Flux Management System)

- Exhibits highly efficient flux recovery and reduces contaminants by applying a new flux collection device.
- Extended PM cycle and improved maintainability
- Equipped with a system for quick replacement of the collection device (for docking)

Reflow of the future that everybody has dreamed of

Please experience to the fullest the innovative functions that

- costs significantly compared to existing systems,
- and operation system allows easy access and reading.

- through a single interface.
- arranged at the front for effective inspection and maintenance,
- contamination

Effective for energy saving by minimizing the change in the internal temperature and reducing power loss by insulating the reflow to optimize thermal efficiency.

Allows the O₂ concentration to be easily converted selectively by standard by applying N₂ flow control interlocked with the PSA. The ESP adjusts the supply of the amount of generated N₂ as much as the amount of N_2 consumed in the oven to reduce the operation of the air compressor, saving the power

 Upgraded the technology for uniform ppm control of entire zones. It is possible to maintain the ppm with the balance using the pressure difference by only injecting a minimum amount of N₂ after shutting offthe inflow of air at the inlet and outlet and sealing the inside of the oven completely.

Allows multi-tasking with 3 split screens on a wide monitor, Easy and convenient screen configuration

 The MMI screen which is configured focusing on the convenience of the user provides a temperature monitoring function, an alarm against operation and maintenance cycles, calibration of the temperature meter and Q_2 meter, as well as a help function that displays the manual necessary for the execution of the program.

The RPPM (Real Time O₂ PPM Profile Monitoring) for which TSM acquired a patent can monitor the status of the O2 ppm in real time inside the reflow without requiring the purchase of a separate profile measuring device and displays the ppm of entire zones by graph,

TSM's WL-RTPM (Real Time Temperature Profile Monitoring solved the problem of the defect of existing sensor methods and problems due to foreign materials. Interlocked with the T-Profiler developed by TSM itself, it can perform real time temperature profiling and make SPEC IN/OUT judgment simultaneously.

All programs (MMI, RTPM and RPPM) were developed by TSM by optimizing them for its reflow. It allows integrated management of all information related to the reflow by providing it to the customers' server

The large capacity FMS optimized for the characteristics of the reflow increases the cleaning interval by collecting the flux efficiently and reduces the down time of the reflow by applying a one touchdocking method and increases the customers' productivity by reducing the PM time.

With its cutting edge ESP that supplies a large quantity of high quality nitrogen built into the reflow, it expands the customers' work space, ensures stable operation and economic benefits of cost saving by controlling the ESP precisely with the PC of the reflow. In addition, components are

 Partial Startup that performs multi-stage control of the heater reduces the basic power cost by minimizing the startup power to reduce the contract power and can reserve the date and time to start the reflow by using the weekly timer, thus further increasing work efficiency.

Its new design maximizes the functionality of the reflow and adopts a structure to maintain the internal temperature of the oven stably and while maximizing the flux discharge. In addition, it secures the space for maintenance at the inlet and outlet sides and applies color and paint with a low discoloration rate and

 The new, special IR+hot air blow heating type heater system satisfies thermal efficiency and performance unlike existing hot air blow heating methods that heat heaters and use a convex current by controlling it with a motor, It maintains d t even at low wind speed owing to its outstanding thermal conductivity. In addition, since it is designed to have high thermal efficiency, heat is transferreddirectly to the base metal, which improves soldering quality, It is suitable for micro pattern processes,

N₂ REFLOW TRN - e SERIES

Automatic N₂ flow control according to the ppm setup Applies an advanced energy saving system

OITUA





TRN 🗆 – e 🗆 🗆 – R [2 Flux Management System Type]

The TRN series reflow developed by TSM through continuous innovation will give customers great satisfaction with its excellent functions and performance as a top model that realizes the econology and humanism for which TSM is aiming.

- The TRN series models features the best of the best in all aspects including energy saving, flux recovery capability, total solution, etc. TSM realized the lowest N2 consumption levels imaginable in its industry by applying a special structure that shields the inside of the oven as well as the system that controls the ppm of all zones uniformly. TSM has played a leading role in reducing N2 consumption in the industry by continuously upgrading and focusing on N2 consumption. Here, its newly developed N₂ flow control system supplies the minimum quantity of N₂ optimized to maintain the set ppm in the oven with the ESP connected to the oven and thus reduces the air consumed in the ESP significantly, reducing the power cost of the air compressor to a great extent. In order to respond to the process that uses solder containing a large amount of flux for the electric parts of automobiles, heaters are installed at the inlet to which flux is mainly adsorbed and the exhaust outlet of the cooling zone in order to prevent flux from remaining and to allow the exhaust to be discharged smoothly. In addition, by allowing the one touch type FMS normally installed at the cooling zone to be installed additionally even in the preheating zone as an option, the flux recovery rate is maximized to allow customers to minimize defects and process management loss.
- Leads the reflow technology by applying a special heater of IR+hot air blow type. TSM's special heater, which combines the convection method that creates convective flow of hot air heated by the heater using a motor to the IR method that transfers the radiant heat of the panel with high thermal efficiency directly to the base metal, maintains dt even at low wind speed, allowing high quality soldering of micro patterns. In addition, it can realize a stable profile because there is little deviation of flow velocity. In particular, while existing plate heaters have burdened customers significantly with their high cost, TSM's panel heater will lead the industry with a new reflow thatboasts both reasonable cost and quality.

Incessant innovation toward the top soldering technology realized the best result.

- By applying the 2 FMS (Flux Management System), the TRN series reflows features the improved flux recovery capability, making its value the highest.
- Realizes energy savings by applying the advanced ESP series N2 generator that can automatically control the N flow rate.
- Leads the reflow technology by applying a special heater of IR+hot air blow type.
- By applying a new design, it secures the space needed for maintenance at the inlet and outlet sides and adopts a color with the lowest discoloration rate which is not easily contaminated.
- The strong blower motor with triple sealing structure and specially structured duct do not allow leakage of any N2.

Keep the inside of the oven clean! Leave it to the 2 FMS (Flux Management System)!

- Completely treats the flux carbonated gas generated during soldering by installing a flux management system (FMS) with high heat exchange capability at the preheater (PH) zone and at the rear of the reflow (2 places).
- an outstanding radiator!
- **Convenient maintenance!** The radiator can be easily removed and installed by one touch. minimizing the workload required for maintenance.





Protects the products from the flying flux generated during soldering by treating the flux gas into liquid state using



The perfect harmony of performance and stability realized a unique and outstanding upgrade.

- In order to continue the reputation of the best selling N70 series,
- a unique and outstanding upgrade has been made, N₂ flow control reduced N₂ consumption and realized energy saving.
- Direct control of the N₂ generator (ESP) in the reflow screen makes it easy to operate the reflow.

Please experience the sophisticated and luxurious N70-e series reflow whose function and specifications have greatly improved upon traditional frames.

- Satisfies both specifications and price the beginning with the function improvement broken from the existing frame, and ensures low running cost and maintainability. Users have not yet tired of the look of the reflows in this series even though they have been in use for many years owing to their gentrified design and ability to paint with low discoloration rate. As a model that has been much loved by customers for many years, the more sophisticated and gentrified N70-series reflow with various functions has upgraded RTPM, RPPM, N2 flow control, FMS whose flux recovery capability is improved, MMI whose operation is convenient, and a triple-sealed blower motor, etc., aiming at optimizing the customers' production capacity.
- The newly designed reflow with its maximized reflow oven function maintains a stable temperature inside the oven, reduces N2 consumption significantly compared to existing reflows by adopting N₂ flow control, and exhibits outstanding performance in maintaining O₂ ppm. Essentially, the cooling zone applies a new design that has further improved the capability of flux recovery at the oven inlet and inside the oven.
- Direct control of the new energy saving N2 generator (ESP series) by the reflow MMI will allow convenient operation of the reflow and reduction of the air compressor power consumption. Sophisticated MMI configuration maximized the convenience of reflow operation,
- Due to changes in energy policies, the watt-hour meter and integrated flow meter used for the monitoring system are provided as an option for the efficient management of N2 and power used by the reflow, helping energy management.







Do you want to know the O₂ concentration in each zone in the N oven?

- to be reduced.
- defects that may occur due to non-uniform ppm.



If it fails to maintain uniform N₂ ppm throughout the zones from the PH1 to the cooling zone, solderability is reduced due to thermal oxidation during soldering, causing product reliability

The real time ppm check system (RPPM), developed and patented by TSM guickly collects the O_2 concentration in each zone and displays it with a real time graph to prevent any

N₂ REFLOW **ES-SERIES**

ES-series reflows realize environment friendliness and power cost reduction by minimizing N2 loss and power consumption



*N*² generator (PSA) built into the reflow allows for innovative space design!

The N₂ generator (PSA) built into the reflow features compact design that needs no separate space, ensuring a pleasant work environment. It is possible to save energy by 20~30% by interlocking the energy saving *N*₂ generator (ESP series) developed by us with the reflow MMI.

Model						
N ₂ Type ((() : Option)						
S	M					

Model Numbering

ES-e 93

There is no other reflows in the world that has been upgraded more than this one. The newly released ES-Series reflow satisfies all of the functionality, economic efficiency and practicality by overcoming its limitations.

- the N₂ purity and flow rate as a built-in type, a first in its industry.
- Realizes unrivaled energy saving by automatically adjusting the N₂ generation quantity being interlocked with the reflow.

Satisfies the need for functionality, economic efficiency and practicality, while its unique design presents an outstanding look even during downtime.

with the reflow MMI.

By automatically controlling the N2 generation quantity with the reflow MMI being interlocked with the N2 generator (ESP-series) optimized for the innovative ES-series reflow, it not only ensures the greatest energy saving in the industry but also realizes minimum N2 consumption and maintains stable ppm with minimum N2 quantity, thus allowing the N2 generator to be controlled by the N2 reflow,





• It is equipped with the most advanced "ESP-series" N2 generator that can control

• By being equipped with the most advanced ESP-series N2 generator that can control N2 purity and flow rate as a built-in type and a first in its industry, this reflow helps customers make better use of space and can operate and use the N2 generator conveniently and stably by controlling it precisely

• By arranging its components at its front for convenient maintenance of the built-in type N₂ generator, the user can perform follow-up management of the N2 generator without difficulty.

The convenience for the user is improved when operating the N₂ generator by adding a function that shows with a message or alarm the operation and maintenance cycle at the time set by the user in the new MMI dedicated to the sophisticated N2 generator whose convenience is maximized,



Provides innovative solutions through energy savings and environmentally friendly policies.

• Has set the standard for power consumption and will continue to be your reliable supporter,

As an output for the achievement of highest performance and econology, the TRA series will satisfy both the economic efficiency and practicality of your business.

• TSM, which performs technical development continuously, realized ultra-low power consumption for the eduction of CO2 emissions in order to realize the econology, the keyword of the TRA series reflows.

The partial start-up which performs the multi-stage control of heaters reduces the contracted receiving power and basic power cost by minimizing the start-up power. It also increases production efficiency by utilizing the weekly timer function which allows reservation of machine operation date and time

In addition, in order to respond to the placement characteristics of various boards, heating efficiency is maximized by multiplying the heating zones and applying a new nozzle structure with improved air flow resistance. It also realizes the best quality by applying an advanced ultra-uniform temperature control system to realize the lowest temperature deviation, The TRA series reflows ensures efficient production of products by applying uniform heating from above and below as well as variable heating from above and below separately, The MMI screen configured for user convenience provides a temperature monitoring function, an alarm for operation and maintenance, a temperature calibration gage, and a help function for program operation, thereby maximizing user convenience for access and reading.

> The RTPM (op), a real time temperature profile monitoring system, provides a variety of information as well as the process index and chart data for the analysis of compatibility and process capability,

Discharge of flux inside the oven

Model

SDW

-f102\$

TRA □ -f82⑤

Why should you use TSM's reflow?

System configuration with outstanding durability Reliable quality

- Energy saving insulation structure
 - Blower motor with triple sealing
- Reliable follow-up management

AIR REFLOW TRA-fSERIES



PSA N₂ Generator

ESP - SERIES

It is possible to freely set the purity and consumption of O₂ through the GUI (Graphic User Interface).



Nicile All All All All All Microgen All All All All
Operation Interlocked with TSM's Reflow Allows control operation from the reflow with the ESP being interlocked with our reflow operation program (MM). The № generator can be controlled by changing the operation conditions by production model (ppm), thus allowing energy savings.
Convenient Touch Panel User convenience has been improved further by applying a convenient touch panel.
ppm 2000 1000 400 0 100 100 10000 1000 1000 1000 1000 1000 1000 1000 1000 1000 1000
N2 Purity Control It is possible to set the purity of produced nitrogen in the ppm unit and control the swing time selectively.
Interlocked Control of Reflow and PSA Interlocked control of the reflow and PSA allows control by ppm, thus allowing outstanding energy savings.

Eco-friendly, low power consuming N² generator effectively responding to customers' needs

N₂ GENERATOR

 $\mathbf{\Sigma}$ Low noise N² generator that can be easily moved and managed owing to its compact structure!

Possible to use space effectively owing to compact design.	Model	Capacity Nm³/Hr (99.99%)	Discharge Pressure (Mpa)	Air Compressor (kw)	Weight (kg)	Dimension D x W x H(mm)
	TPM-N1R-99	1			300	860 × 400 × 1,000
Free Installation and Relocation Possible to be freely moved by installing casters on all types of N2 generators and	TPM-N2R-99	2		1.5 3.7	300	860 x 400 x 1,000
	TPM-N3R-99	3	0.5		310	1,100 × 530 × 890
	TPM-N4R-99	4	0.0		330	1,100×530×890
	TPM-N5R-99	5			350	1,100 × 530 × 890
therefore to use space effectively.		5			000	1,100 × 300 × 650
Low Noise	▷ Moving PSA	Туре В				
Can be used indoors with no problem	TPM-N10R-99	10			600	1,480 x 560 x 1,340
owing to low operational noise.	TPM-N12R-99	12		7.5	700	1,480 x 560 x 1,34
0	TPM-N10RT-99	10		7.5	600	1,510 x 420 x 1,36
Convenient Manipulability	TPM-N12RT-99	12	0.5		700	1,620 x 470 x 1,33
Operation and movement can be easily	TPM-N15RT-99	15	0.0		800	1,708 x 520 x 1,36
managed and controlled with the display	TPM-N15RL-99	15		11	700	1,300 x 520 x 1,36
panel. O2 purity is displayed.	TPM-N17RL-99	17			900	1,300 x 520 x 1,30 1,480 x 560 x 1,34
N ² Generator that sup and stably! Easy Maintonanco	plies high ▷ TPC-Type I	PSA				
- ·			gen to the N2 Discharge Pressure (Mpa)	reflow con	Weight (kg)	Dimension D x W x H(mm)
and stably! Easy Maintenance	> TPC-Type I	PSA Capacity Nm³/Hr	Discharge Pressure	Air Compressor	Weight	Dimension
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve.	▷ TPC-Type I Model	PSA Capacity Nm ³ /Hr (99.99%)	Discharge Pressure	Air Compressor (kw)	Weight (kg)	Dimension D x W x H(mm)
and stably! Easy Maintenance Allows easy maintenance by applying a	▷ TPC-Type I Model TPC-N30R-99	PSA Capacity Nm³/Hr (99.99%) 30	Discharge Pressure	Air Compressor (kw) 22 30	Weight (kg) 1,500	Dimension D x W x H(mm) 1,400 x 900 x 2,10
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve.	 D TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N50R-99 TPC-N60R-99 TPC-N60R-99 	PSA Capacity Nm²/Hr (99.99%) 30 40 50 60	Discharge Pressure (Mpa)	Air Compressor (kw) 22	Weight (kg) 1,500 1,900 2,400 2,700	Dimension D x W x H(mm) 1,400 x 900 x 2,10 1,450 x 950 x 2,30 1,500 x 1,100 x 2,4
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple	D TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N50R-99	PSA Capacity Nm²/Hr (99.99%) 30 40 50	Discharge Pressure (Mpa)	Air Compressor (kw) 22 30	Weight (kg) 1,500 1,900 2,400 2,700 3,200	Dimension D x W x H(mm) 1,400 x 900 x 2,10 1,450 x 950 x 2,30 1,500 x 1,100 x 2,4 1,650 x 1,100 x 2,6 1,800 x 1,200 x 2,8
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple Can supply high purity nitrogen gas by	▷ TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N50R-99 TPC-N80R-99 TPC-N80R-99	PSA Capacity N#//Hr (99.99%) 30 40 50 60 80	Discharge Pressure (Mpa)	Air Compressor (kw) 22 30 37	Weight (kg) 1,500 1,900 2,400 2,700 3,200	Dimension D x W x H(mm) 1,400 x 900 x 2,10 1,450 x 950 x 2,30 1,500 x 1,100 x 2,4 1,650 x 1,100 x 2,6
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple Can supply high purity nitrogen gas by only supplying power.	▷ TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N50R-99 TPC-N50R-99 TPC-N50R-99 ▷ TP-Type PS	PSA Capacity Nm ² /Hr (99.99%) 30 40 50 60 80 SA	Discharge Pressure (Mpa)	Air Compressor (kw) 22 30 37	Weight (kg) 1,500 1,900 2,400 2,700 3,200 ** N2 Se	Dimension D x W x H(mm) 1,400 x 900 x 2,10 1,450 x 950 x 2,30 1,500 x 1,100 x 2,4 1,650 x 1,100 x 2,6 1,800 x 1,200 x 2,8 rvice Tank는 포함되지
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple Can supply high purity nitrogen gas by only supplying power. Can supply high purity and	▷ TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N50R-99 TPC-N80R-99 TPC-N80R-99 ▷ TP-Type PS TP-N30R-99	PSA Capacity Nm ² /Hr (99.99%) 30 40 50 60 80 80 SA 30	Discharge Pressure (Mpa)	Air Compressor (kw) 22 30 37 55	Weight (kg) 1,500 1,900 2,400 2,700 3,200 ≭ №2 Se 1,520	Dimension D x W x H(mm) 1,400 x 900 x 2,10 1,450 x 950 x 2,30 1,500 x 1,100 x 2,4 1,650 x 1,100 x 2,6 1,800 x 1,200 x 2,8 rvice Tank는 포함되지 1,400 x 1,520 x 2,10
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple Can supply high purity nitrogen gas by only supplying power. Can supply high purity and	 ▷ TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N80R-99 TPC-N80R-99 TPC-N80R-99 TP-Type PS TP-N30R-99 TP-N40R-99 	PSA Capacity Nm ² /Hr (99.99%) 30 40 50 60 80 80 SA 30 40	Discharge Pressure (Mpa)	Air Compressor (kw) 22 30 37 55 22	Weight (kg) 1,500 1,900 2,400 2,700 3,200 ≭ № 2 Se 1,520 1,830	Dimension D x W x H(mm) 1,400 x 900 x 2,10 1,500 x 1,100 x 2,4 1,650 x 1,100 x 2,4 1,650 x 1,100 x 2,6 1,800 x 1,200 x 2,5 rvice Tank는 포함되지 1,400 x 1,520 x 2,10 1,450 x 1,600 x 2,30
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple Can supply high purity nitrogen gas by only supplying power. Can supply high purity and	 ▷ TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N80R-99 TPC-N80R-99 TPC-N80R-99 TPC-N80R-99 TP-N30R-99 TP-N30R-99 TP-N40R-99 TP-N50R-99 	PSA Capacity Nm ² /Hr (99.99%) 30 40 50 60 80 80 SA 30 40 50	Discharge Pressure (Mpa) 0.5	Air Compressor (kw) 22 30 37 55 22	Weight (kg) 1,500 2,400 2,700 3,200 ≭N2 Se 1,520 1,830 2,340	Dimension D x W x H(mm) 1,400 x 900 x 2,1(1,450 x 950 x 2,3(1,500 x 1,100 x 2,4 1,650 x 1,100 x 2,6 1,800 x 1,200 x 2,6 1,800 x 1,200 x 2,5 rvice Tank는 포함되지 1,400 x 1,520 x 2,1(1,450 x 1,600 x 2,3(1,500 x 1,750 x 2,44)
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple Can supply high purity nitrogen gas by only supplying power. Can supply high purity and	 ▷ TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N80R-99 TPC-N80R-99 TPC-N80R-99 TPC-N80R-99 TP-N30R-99 TP-N40R-99 TP-N50R-99 TP-N50R-99 TP-N60R-99 TP-N60R-99 	PSA Capacity Nm*/Hr (99.99%) 30 50 60 80 SA 30 40 50 60 80	Discharge Pressure (Mpa)	Air Compressor (kw) 22 30 37 55 55 22 30 37	Weight (kg) 1,500 2,400 2,700 3,200 × № 2 Se 1,520 1,830 2,340 2,610	Dimension D x W x H(mm) 1,400 x 900 x 2,1(1,450 x 950 x 2,3(1,500 x 1,100 x 2,4 1,650 x 1,100 x 2,6 1,800 x 1,200 x 2,5 rvice Tank는 포함되지 1,400 x 1,520 x 2,1(1,450 x 1,600 x 2,3(1,500 x 1,750 x 2,4(1,650 x 1,850 x 2,6(
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple Can supply high purity nitrogen gas by only supplying power. Can supply high purity and	 ▷ TPC-Type I Model TPC-N40R-99 TPC-N40R-99 TPC-N60R-99 TPC-N80R-99 TPC-N80R-99 TP-N40R-99 TP-N40R-99 TP-N50R-99 TP-N60R-99 TP-N80R-99 TP-N80R-99 TP-N80R-99 	PSA Capacity Nm//Hr (99.99%) 30 40 50 60 80 SA 30 40 50 60 80 80	Discharge Pressure (Mpa) 0.5	Air Compressor (kw) 22 30 37 55 55 22 30 37 37 55	Weight (kg) 1,500 1,900 2,700 3,200 ≭N≥ Se 1,520 1,830 2,340 2,610 3,100	Dimension D x W x H(mm) 1,400 x 900 x 2,1 1,500 x 1,100 x 2,4 1,650 x 1,100 x 2,4 1,650 x 1,100 x 2,6 1,800 x 1,200 x 2,6 1,400 x 1,520 x 2,11 1,450 x 1,600 x 2,31 1,500 x 1,750 x 2,41 1,650 x 1,850 x 2,66 1,800 x 2,050 x 2,86
and stably! Easy Maintenance Allows easy maintenance by applying a nighly reliable solenoid valve. Simple Can supply high purity nitrogen gas by only supplying power. Can supply high purity and	 ▷ TPC-Type I Model TPC-N30R-99 TPC-N40R-99 TPC-N50R-99 TPC-N80R-99 TPC-N80R-99 ○ TP-Type PS TP-N30R-99 TP-N40R-99 TP-N40R-99 TP-N50R-99 TP-N80R-99 TP-N90R-99 TP-N90R-99<!--</td--><td>PSA Capacity Nm²/Hr (99.99%) 30 40 50 60 80 SA 30 40 50 60 80 80 100</td><td>Discharge Pressure (Mpa) 0.5</td><td>Air Compressor (kw) 22 30 37 55 22 30 37 55 37 55 75</td><td>Weight (kg) 1,500 2,400 2,700 3,200 * N2 Se 1,520 1,830 2,340 2,610 3,100 3,200</td><td>Dimension D x W x H(mm) 1,400 × 950 × 2,30 1,500 × 1,100 × 2,4 1,650 × 1,100 × 2,6 1,800 × 1,200 × 2,6 1,800 × 1,200 × 2,6 1,400 × 1,520 × 2,1 1,450 × 1,600 × 2,3 1,500 × 1,750 × 2,4 1,800 × 1,850 × 2,6 1,800 × 2,050 × 2,8 1,850 × 1,700 × 3,0</td>	PSA Capacity Nm ² /Hr (99.99%) 30 40 50 60 80 SA 30 40 50 60 80 80 100	Discharge Pressure (Mpa) 0.5	Air Compressor (kw) 22 30 37 55 22 30 37 55 37 55 75	Weight (kg) 1,500 2,400 2,700 3,200 * N2 Se 1,520 1,830 2,340 2,610 3,100 3,200	Dimension D x W x H(mm) 1,400 × 950 × 2,30 1,500 × 1,100 × 2,4 1,650 × 1,100 × 2,6 1,800 × 1,200 × 2,6 1,800 × 1,200 × 2,6 1,400 × 1,520 × 2,1 1,450 × 1,600 × 2,3 1,500 × 1,750 × 2,4 1,800 × 1,850 × 2,6 1,800 × 2,050 × 2,8 1,850 × 1,700 × 3,0
and stably! Easy Maintenance Allows easy maintenance by applying a highly reliable solenoid valve. Simple Can supply high purity nitrogen gas by only supplying power. Can supply high purity and	 ▷ TPC-Type I Model TPC-N40R-99 TPC-N40R-99 TPC-N60R-99 TPC-N80R-99 TPC-N80R-99 TP-N40R-99 TP-N40R-99 TP-N50R-99 TP-N60R-99 TP-N80R-99 TP-N80R-99 TP-N80R-99 	PSA Capacity Nm//Hr (99.99%) 30 40 50 60 80 SA 30 40 50 60 80 80	Discharge Pressure (Mpa) 0.5	Air Compressor (kw) 22 30 37 55 55 22 30 37 37 55	Weight (kg) 1,500 1,900 2,700 3,200 ≭N≥ Se 1,520 1,830 2,340 2,610 3,100	Dimension D x W x H(mm) 1,400 x 900 x 2,1 1,450 x 950 x 2,3 1,500 x 1,100 x 2, 1,650 x 1,100 x 2, 1,800 x 1,200 x 2,5 rvice Tank는 포함되지 1,400 x 1,520 x 2,1 1,450 x 1,600 x 2,3 1,500 x 1,750 x 2,4 1,650 x 1,850 x 2,6

Air Filter
Air Filter
Adsorpti



\langle N_2 Generator(TP - Type) + N_2 Reflow Flow Diagram
 \langle

Filter

ant Air Dru



Type Air Drye

t Room

(Inspection and Certifying Test)









TPC - Type



TP – Type



EQUIPMENT

		N70-e	ES-	TRN-e	N70-i
Mechanism	Basic Sheath Heater	•	•	•	•
	Special Plate Heater	-	-		-
	Separable Blower Motor	-	•	•	-
	Triple Sealed Blower Motor				
	Detachable FMS	•	•	•	•
	C/V chain + Center Support				
	C/V chain + Mesh				
	Special Attachment Chain				
	Mesh Belt Only Type				
	Low Vibration Mesh Belt				
Operation	C/V chain + Two CenterSupport				
	C/V Width Semi Auto				
	C/V Width Full Auto				
	Torque Limit (Overload Prevention)				
	Dual Type (Simultaneous F/R Control)				
	Dual Type (Independent F/R Control)				
	N2 Quick charge				
	Cooling Zone Heater				
	RTPM				
	RPPM				
	Watt Hour Meter				
	Integrated Flow Meter				
	Detection Sensor of B/M Rotation				
Convenient	PSA Built in type	-			_
Function	ND System	•	٠	•	
	New MMI + ESP Interlock				-
	N2 Flow Rate Control	٠	•	•	-
	O2 Flow Control	-	-	-	
	Bar Code Function				
	New UPS (Charge Indicator + Communication Function)				
	Digital Flow Meter				
	SMEMA				
011	CE				
Others	SECS/GEM				
	Dual Monitor				
	T-Profiler				
	●:Stand	ard ▲:C	ption -	– :Not Ap	plicable

Contact for Business Services and Purchasing

Microtronic M. V. GmbH Kleingrötzing 1 D-84494 Neumarkt-Sankt Veit



Tel: +49 8722-9620-0 Fax: -30

Email: tsm@microtronic.de WEB: www.microtronic.de









Factory in Sihwa MTV Complex



57, MTV 26-ro 20beon-gil, Siheung-si, Gyeonggi-do, 15118 Rep. of KOREA TEL : +82-31-499-4895 FAX : +82-31-499-4895 E-mail : sales@tsms.kr http://www.tsms.kr

